

TECHSPEC® 20mm Dia., Uncoated, Linear Glass Polarizer (XP42)



Stock **#19-643** 3-4 DAYS

- 1 + **£110.50**

ADD TO CART

Qty 1-9
£110.50

Qty 10+
£97.75

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Diameter (mm):
20.00

Extinction Ratio:
9000:1 @546nm

Substrate: XP42 Laminated Between Glass
Operating Temperature (°C): -10 to +55
Thickness (mm): 2.00 ±0.10
Transmission (%): 42 @ 546nm
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.00/-0.20
Construction: Laminated Glass Polarizing Film
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98 @ 546nm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant