

TECHSPEC® 20mm Diameter x -40 FL, VIS 0° Coated, Plano-Concave Lens



Stock **#47-909** ☐ In Stock
[Other Coating Options](#)

1 **£36.98**

ADD TO CART

Qty 1-9
£36.98
Qty 10+
£33.36
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-40.00
Substrate: N-BK7
f#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -42.31
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 19.00
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 5.92
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -20.67
Surface Quality: 40-20
Damage Threshold, Reference: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant