

TECHSPEC® 20mm, Enhanced Aluminum Coated, N-BK7 90° Specialty Mirror



Stock **#49-414** ☐ In Stock

-

1

+

£127.50

ADD TO CART

Qty 1-5

£127.50

Qty 6+

£102.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
19.4

Coating:
Enhanced Aluminum (450-650nm)

Substrate: ☐
N-BK7

Surface Quality: 40-20
Type: Right Angle Mirror
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture (%): 90.00
Length of Hypotenuse (mm): 28.30
Length of Legs (mm): 20.00
Coating Specification: R _{avg} >95% @ 450 - 650nm
Wavelength Range (nm): 450 - 650
Surface Flatness (P-V): λ/8
Coating Type: Metal
Damage Threshold, Reference:  0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant