

TECHSPEC[®] 20mm NIR, 30R/70T, Non-Polarizing Cube Beamsplitter



Stock #13-424 3-4 DAYS

-

1

+

£203.15

ADD TO CART

Qty 1-5
£203.15
Qty 6+
£160.65
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:	NIR
Coating Specification:	R _{avg} <0.5% @ 720 - 1080nm
Construction:	Cube
Dimensions (mm):	20.0 x 20.0 x 20.0 ±0.1
Reflection/Transmission Ratio (R/T):	30/70
Substrate:	N-BK7
Surface Flatness (P-V):	λ/8
Surface Quality:	40-20
Type:	Non-Polarizing Beamsplitter
Wavelength Range (nm):	720 - 1080
Ts-Tp :	<6%
Absolute Transmission (%):	65 ±10
Average Transmission (%):	65 ±5

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View