

TECHSPEC[®] 20mm NIR, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #47-124 3-4 DAYS

-

1

+

£236.30

ADD TO CART

Qty 1-5
£236.30
Qty 6+
£185.30
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: NIR
Coating Specification: R_{avg} <0.5% @ 720 - 1080nm
Construction: Cube
Dimensions (mm): 20.0 x 20.0 x 20.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 720 - 1080
Ts-Tp : <6%
Absolute Transmission (%): 45 ±10
Average Transmission (%): 45 ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View