

220mm Dia x 100mm FL Alum. Coated, Parabolic Reflector



Stock #68-793

3-4 DAYS



1



£709.75

ADD TO CART

Qty 1-10

£709.75

Qty 11+

£624.32

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: BOROFLOAT®

Diameter (mm): 220.00 +0.0/-0.5

Focal Length FL (mm): 100.00

Aperture (f#):

0.455
Coating: Protected Aluminum (400-700nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating Type: Metal
Center Hole Diameter (mm): No Center Hole
Height (mm): 33.0
Type: Parabolic Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View