

220nm CWL, 10nm FWHM, 25mm Mounted Diameter



Stock #67-802 3-4 DAYS

⊖ 1 ⊕ **£272.85**

ADD TO CART

Qty 1-9
£272.85

Qty 10+
£245.06

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Diameter (mm): 25.00 +0.00/-0.25
Angle of Incidence (°): 0
Optical Density OD (Average): ≥4.0

Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 220.00 +3.0/-0.0
Center Wavelength CWL Tolerance (nm): +3.0/-0.0
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): >12
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: Clinical Chemistry
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.9

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant