

## 2.25" x 12.0", 2.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock #46-616 **20+ In Stock**

⊖ 1 ⊕ £79<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	£79.60 each
Qty 11-49	£71.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Fresnel Lens **Type:**

### Physical & Mechanical Properties

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

2.25 x 12.00 **Dimensions (inches):**

57.15 x 304.8 **Dimensions (mm):**

2.0 x 12.0 **Effective Size (inches):**

±0.020 **Thickness Tolerance (inches):**

### Optical Properties

50.80 **Effective Focal Length EFL (mm):**

Acrylic **Substrate:**

Uncoated **Coating:**

400 - 1100 **Wavelength Range (nm):**

2.00 **Effective Focal Length EFL (inches):**

200.00 **Groove Density (grooves/inch):**

1.49 **Index of Refraction (n<sub>d</sub>):**

85 (Typical) **Transmission (%):**

### Environmental & Durability Factors

80 (Maximum) **Operating Temperature (°C):**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 242:**

## Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

## Technical Information

