

TECHSPEC® 22mm Aluminum Coated, Littrow Dispersion Prism



30° - 60° - 90° Littrow Dispersion Prisms

Stock **#43-673** 3-4 DAYS



1



£72.25

ADD TO CART

Qty 1-5

£72.25

Qty 6+

£57.80

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Protected Aluminum (400-2000nm)

Substrate: ☐
[N-BK7](#)

Length (mm):
22.00

Surface Quality: 80-50
Type: Littrow Prism
Dimensional Tolerance (mm): ±0.13
Angle Tolerance (arcmin): ±10
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Coating Specification: R _{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 60
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): 1λ @ 632.8nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View