

SCHOTT RG-715, 22mm CA, C-Mount Longpass Glass Color Filter



22mm CAC-Mount Longpass Glass Color Filter

Stock **#13-036** ■ **In Stock**

⊖

1

⊕

£79.05

ADD TO CART

Qty 1-9
£79.05

Qty 10+
£70.55

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 ±0.38

Clear Aperture CA (mm):
22.0

Cut-Off Position λ_c (nm):
715±9

Cut-On Wavelength (nm): 715.00
Density (g/cm³): 2.76
Glass/Filter Number: SCHOTT RG715
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Passband Limit 1 λ_{p1} (nm): 810.00
Spectral Transmittance t_p (%): 96.00
Stopband Limit λ_s(nm): 620.00
Surface Quality: 80-50
Transformation Temperature (°C): 532.00
Type: Longpass Filter
Wavelength: IR
Reflection Factor P_d: 0.91
Substrate Thickness (mm): 3.00 ±0.2
Thread Type: C-Mount
Total Length (mm): 20.3
Mount Diameter (mm): 30.0
Filter Included: #46-065
Mount Included: #56-353

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View