

## 240mm Length, Adjustable Laser Holder



#56-332, #56-333

Stock **#56-333 7 In Stock**

⊖ 1 ⊕ £300<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-4    | £300.00 each                  |
| Qty 5-25   | £265.20 each                  |
| Qty 26-49  | £244.24 each                  |
| Need More? | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Adjustable - Tilt **Type:**  
Cylindrical Tube **Type of Optics:**

### Physical & Mechanical Properties

**Length (mm):**

240.00

1020

Weight (g):

Construction:

Black Anodized Aluminum

Twin Ring Mount Adjustment Screw Pitch (mm):

0.5

Tilt Angle (°):

±2

### Threading & Mounting

Size of Compatible Optics (mm):

20.0 - 55.0

Compatible Post:

M6 x 1.0

### Regulatory Compliance

RoHS 2015:

Exempt

Certificate of Conformance:

[View](#)

Reach 247:

[Contains SVHC\(s\)](#)

## Product Details

- Twin Ring Mount Design
- Fixed and Adjustable Versions
- Ideal for He-Ne Lasers
- [Posts](#) and [Post Holders](#) Required for Mounting

Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Mounting hole is M6 x 1.0

## Technical Information

