

240mm Length, Fixed Laser Holder



#54-990, #54-991

Stock **#54-991** 20+ In Stock

-

1

+

£181⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£181.60 each
Qty 5-25	£160.48 each
Qty 26-49	£147.84 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fixed	Type:
Cylindrical Tube	Type of Optics:

Physical & Mechanical Properties	
	Length (mm):

240.00	
660	Weight (g):
Black Anodized Aluminum	Construction:
Twin Ring Mount Adjustment Screw Pitch (mm):	
0.5	

Threading & Mounting

20.0 - 55.0	Size of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- Twin Ring Mount Design
 - Fixed and Adjustable Versions
 - Ideal for He-Ne Lasers
 - [Posts](#) and [Post Holders](#) Required for Mounting
- Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.
- Mounting hole is M6 x 1.0

Technical Information

