

24.9mm Dia. x 17mm FL, Aspheric Condenser Lens



Stock **#19-516** 3-4 DAYS

[Other Coating Options](#)

- 1 +

£31.45

ADD TO CART

Qty 1-10
£31.45

Qty 11+
£28.05

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
24.90 +0.0/-0.2

Effective Focal Length EFL (mm):
17.00

Numerical Aperture NA:
0.73

Back Focal Length BFL (mm): 9.8
Substrate: □ H-K51
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 22.41
Edge Thickness ET (mm): 1.90
Center Thickness CT (mm): 11.00 ±0.30
f/#: 0.68
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 24.9
Radius R ₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View