

## 25 Gauge (50 Count), UV Blocking Tapered Tips



25 Gauge (50 Count), UV Blocking Tapered Tips, #55-065

Stock **#55-065** 7 In Stock

-

1

+

£49<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £49.20 each                   |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

### SPECIFICATIONS

General

25 Gauge, Red Color

Type:

Physical & Mechanical Properties

0.25

Inner Diameter (mm):

0.51

Outer Diameter (mm):

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Empty Barrels are Available in Clear, Amber, and Opaque Versions
- Tips are Available in Plastic and Steel
- [Dispensing Guns](#) and [Pre-Loaded Norland Adhesive Barrels](#) are Also Available

Dispenser barrels, tips, and other accessories are available for use with dispensing guns and hand plungers. Dispenser Barrels are available in a clear version for normal fluids, an amber version for UV-curing fluids, and an opaque version for light sensitive fluids. Dispenser tips are available in plastic and steel to ensure varying levels of controllable deposits without leakage.

**Note:** Barrels, tips, and adhesive are sold separately from [dispensers](#). [Pre-loaded Norland adhesive barrels](#) are also available.