

25 x 25 x 4mm MgF₂ Coated, N-BK7 Window



Stock **#27-852** CLEARANCE 3-4 DAYS

-

1

+

£12.71

ADD TO CART

Qty 1+

£12.71

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Abbe Number (v_d):

64.17

Bevel:

Protective as needed

Clear Aperture CA (mm):

22.50 x 22.50

Dimensions (mm):

25.00 x 25.00

Thickness (mm):

4.00 ±0.20

Coating: MgF ₂ (400-700nm)
Coating Specification: MgF ₂ : ¼λ @ 550nm, R _{avg} ≤ 1.75% @ 400 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): ≤5
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Accuracy: 1λ
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 82
Length (mm): 25.00
Width (mm): 25.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View