

25 x 25mm 120 Grit Ground Glass Diffuser



Stock **#83-381** ☐ In Stock

- 1 + **£17.43**

ADD TO CART

Qty 1-10
£17.43
Qty 11+
£15.30
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating: Uncoated
Dimensional Tolerance (mm): ±0.25
Dimensions (mm): 25.00 x 25.00
Edges:

Cut Edges
Grit: 120
Substrate: Float Glass
Thickness (mm):1.60
Type:Ground Glass Diffuser
Wavelength Range (nm):350 - 2000
Width (mm):25.00
Note:Sandblasted on first surface
Length (mm):25.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant