

## 25 x 25mm Broadband Hybrid Diffuser



Broadband Hybrid Diffusers

Stock **#36-613** **20+ In Stock**

£40.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	£40.00 each
Qty 11-49	£31.80 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Opal Diffuser Type:

#### Physical & Mechanical Properties

25.00 x 25.00 ±0.3 Dimensions (mm):

120 Grit:

1.75 ±0.1      **Thickness (mm):**

25.00      **Width (mm):**

25.00      **Length (mm):**

## Optical Properties

Uncoated      **Coating:**

White Diffusing Glass      **Substrate:**

400 - 1100      **Wavelength Range (nm):**

## Regulatory Compliance

[Compliant](#)      **RoHS 2015:**

[Compliant](#)      **Reach 211:**

[View](#)      **Certificate of Conformance:**

## Product Details

- Surface Treated Semi-Opaque White Glass
- Two Mechanisms of Scatter
- Excellent Scattering into the NIR

Broadband Hybrid Diffusers are semi-opaque diffusers designed to scatter efficiently from the UV to the NIR. Featuring surfaces sandblasted with 120-grit and a 1.75mm thick scattering medium, these diffusers uniquely offer two mechanisms of scatter. Each scatter mechanism has its own wavelength dependency, and when combined on a single optic, produce a diffuser that scatters across a wide spectral region. Broadband Hybrid Diffusers are ideal for applications that require high scatter for even illumination and can be used as view screens.

## Compatible Mounts

;