

SCHOTT KG3, 25mm Sq., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #49-089 □ In Stock

-

1

+

£38.25

ADD TO CART

Qty 1-10

£38.25

Qty 11+

£34.00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
25.0 x 25.0

Density (g/cm³):
2.53

Glass/Filter Number:

[SCHOTT KG3](#)

Substrate: ☐
Heat Absorbing Glass

Length (mm):
25.00

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d :
1.51

Surface Quality:
60-40

Transformation Temperature (°C):
581

Thickness (mm):
3.00 ±0.38

Type:
IR Cut-Off Filter

Width (mm):
25.00

Dimensional Tolerance (mm):
±0.25

Reflection Factor P_d :
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

Reach 181:
[Compliant](#)

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)