

TECHSPEC® 25 x 35mm Enhanced Aluminum, λ/4 Mirror



Stock **#32-513** ☐ In Stock

1 **£53.13**

ADD TO CART

Qty 1-5
£53.13
Qty 6+
£42.50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Fine Ground

Surface Quality: 60-40
Dimensions (mm): 25.0 x 35.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Length (mm): 35.00
Width (mm): 25.00
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant