

25 x 38mm, 25R/75T, Plate Beamsplitter



Stock #31-437 3-4 DAYS

- 1 + **£46.75**

ADD TO CART

Qty 1-9
£46.75
Qty 10+
£35.70
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: Uncoated

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 25.0 x 38.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 25/75
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant