

TECHSPEC[®] 25/25.4mm Diameter, C-Mount Thick Optic Mount



Stock **#56-354** **20+ In Stock**

-

1

+

£85⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£85.80 each
Qty 5-9	£76.17 each
Qty 10-25	£70.30 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Fixed	Type:
Circular	Type of Optics:
Optic Mount (Fixed)	Function:
Physical & Mechanical Properties	
24.2	Extension Length (mm):
Black Anodized Aluminum (6061 T6)	Construction:
28.2	Total Length (mm):
30.0	Outer Diameter (mm):
22.00	Clear Aperture CA (mm):
11.5	Max. Thickness of Compatible Optics (mm):
3.3	Min. Thickness of Compatible Optics (mm):
Threading & Mounting	
25.0 - 25.4	Diameter of Compatible Optics (mm):
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

PRODUCT DETAILS

25/25.4mm holder is a 3 part assembly and adds 24.2mm to the system length.

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x32TPI, M12 x0.5, or M42 x0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

TECHNICAL INFORMATION

