

25/25.4mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts



#17-523: 25/25.4mm Dia., Kinematic Mount, 3-Screws



Stock **#17-523** [CONTACT US](#)

- 1 + **£116.88**

ADD TO CART

Qty 1+

£116.88

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
25.0 - 25.4

Number of Adjustment Screws:

Clear Aperture CA (mm): 22.9
Travel (mm): Z-Axis: 8
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Contents of Kit: #58-854 , #15-850
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 1.8
Pointing Stability (μrad): 1.3
Optical Axis Height (mm): 127.00
Post Diameter (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
