

25.4mm Clear Aperture 33R/67T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-480** ☐ In Stock



1



£184.45

ADD TO CART

Qty 1-10

£184.45

Qty 11+

£156.82

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
25.4

Coating:
Dielectric

Coating Specification:

33/67 @ 400 - 700nm
Construction: Pellicle
Diameter (mm): 34.90
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 4.76
Reflection/Transmission Ratio (R/T): 33/67 $\pm$ 5%
Substrate: ☐ Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Wavelength Range (nm): 400 - 700
Mounting Threads: 2-56
Thickness (μm): 2 +0.3/-0.0

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View