

25.4mm Dia. 302nm $\lambda/4$ Quartz Waveplate Zero Order



Stock #35-133 CLEARANCE 3-4 DAYS

-

1

+

£518.50

ADD TO CART

Qty 1-5
£518.50
Qty 6+
£418.20
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
15.00

Coating:
Laser V-Coat (302nm)

Design Wavelength DWL (nm):
302

Diameter (mm):

25.40 +0.0/-0.2
Substrate: Crystal Quartz
Retardance: $\lambda/4$
Surface Quality: 10-5
Thickness (mm): 7.80
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: $\lambda/10$ for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: $\pm\lambda/100$
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View