

TECHSPEC® 25.4mm Dia., 6.35mm Thick, 355nm, λ/10 N-BK7 Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock **#38-933** CLEARANCE 3-4 DAYS

⊖ 1 ⊕

£93.46

ADD TO CART

Qty 1+

£93.46

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
22.86

Coating:
Laser V-Coat (355nm)

Design Wavelength DWL (nm):
355

Diameter (mm): 25.40 +0.00/-0.10
Substrate: N-BK7
Index of Refraction n_d: 1.516
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 64.17
Coating Specification: R_{abs} <0.25% @ 355nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 7.5 J/cm² @ 355nm, 20ns, 20Hz
Edges: Fine Ground

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View