

25.4mm Dia f/0.75 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#33-258** 3-4 DAYS

-

1

+

£51.00

ADD TO CART

Qty 1-10

£51.00

Qty 11+

£42.50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
19.10 @ 632.8nm

Numerical Aperture NA: 0.67
Back Focal Length BFL (mm): 12.7
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: Uncoated
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4.00
Center Thickness CT (mm): 12.22
f/#: 0.75
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 99.57
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View