

TECHSPEC®

25.4mm Dia x 100mm FL, Uncoated Imaging Grade PCX Cylinder Lens



Stock #34-613

3-4 DAYS

-

1

+

£75.65

ADD TO CART

Qty 1-5
£75.65
Qty 6+
£60.35
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

25.40 +0.0/-0.025

Effective Focal Length EFL (mm):

100.00

Substrate:

N-BK7

f/#: 4.00
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 97.92
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.16
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86
Edge Thickness ET (mm): 1.58
Focal Length Tolerance (%): ±1
Radius R₁ (mm): 51.68
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View