

25.4mm Dia. x -76.2mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) PCV Lens
| CF-PC-25-76

See More by [ISP Optics](#)



Stock #24-783 3-4 DAYS

-

1

+

£131.75

ADD TO CART

Qty 1-9
£131.75
Qty 10+
£118.58
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.13

Effective Focal Length EFL (mm):
-76.20 @ 5µm

Substrate: Calcium Fluoride (CaF₂)
f#: 3.00
Numerical Aperture NA: 0.17
Coating: Uncoated
Type: Plano-Concave Lens
Wavelength Range (nm): 300 - 8000
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00 ±0.20
Centering (arcmin): <3
Clear Aperture CA (mm): 22.86
Edge Thickness ET (mm): 4.80
Focal Length Tolerance (%): ±2
Model Number: CF-PC-25-76
Radius R₁ (mm): -30.70
Surface Quality: 60-40
Irregularity (P-V) @ 632.8nm: λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View