

25.4mm Travel, Metric Micrometer, Solid Top 44.4mm Stage



Stock #55-461

3-4 DAYS

-

1

+

£921.40

ADD TO CART

Qty 1+
£921.40

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:

Linear (X)

Guide System:

Ball Bearing

Type of Drive:

Digital Micrometer (Metric)

Drive Orientation:

Center Drive

Type:

Metric

Stage Size (mm): 44.4 x 44.4
Travel (mm): 25
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (mm): 0.001
Load Capacity, Normal (kg): 11
Load Capacity, T_a (kg): 4.5
Load Capacity, T_b (kg): 2.3
Note: Solid Top
Stage Size (inches): 1.75 x 1.75
Straight Line Accuracy (μm): 2 per 25 mm of travel
Weight (g): 450

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View