

25.8mm Outer Diameter, Precision Pinhole Mount



25.8mm Outer Diameter, Precision Pinhole Mount, #53-287

Stock **#53-287** 20+ In Stock

-

1

+

£44⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	£44.40 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Requires one pinhole aperture	Note:
Physical & Mechanical Properties	
25.8	Outer Diameter (mm):
Black Anodized Aluminum	Construction:
Threading & Mounting	

Diameter of Compatible Optics (mm):	
9.5	
Barrel Thread:	
RMS (0.8" - 36 TPI)	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	

Product Details

- Provides Mechanical Support for [Precision Pinholes](#)
- Uses a Retainer Ring to Minimize Mechanical Stress
- Adaptable to [C-Mount Components](#)

With a 1.02" diameter, the Precision Pinhole Mount features a retainer ring for the secure placement of 3⁄8" (9.5mm) diameter unmounted [precision pinholes](#). The back face has a male external RMS thread (20.32mm x 36TPI). When used with [#03-627](#) threaded objective ring mount, the Precision Pinhole Mount can easily mount to [C-mount components](#). A two piece ring mount with a 1⁄4-20 mounting hole is available to adapt the Precision Pinhole Mount to standard [optical breadboards and posts](#).