

TECHSPEC®

25mm 850nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#47-050**

3-4 DAYS



1



£242.25

ADD TO CART

Qty 1-5

£242.25

Qty 6+

£189.55

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification: R_{abs} <0.25% @ 850nm
Construction: Cube
Design Wavelength DWL (nm): 850
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%): >95
S-Polarization Reflection (%): >99.5
Substrate: N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View