

TECHSPEC® 25mm Cage System Iris, 0.8 - 12mm Aperture



Stock #88-199 **6 In Stock**

- 1 + £124.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£124.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Iris **Function:**

Number of Leaves: 10 **Note:**

Physical & Mechanical Properties

25.0 **Compatible Plate Inner Diameter (mm):**

17.20 **Length (mm):**

0.8 - 12	Inner Diameter (mm):
Black Anodized Aluminum	Construction:
31.5 Dia.	Dimensions (mm):
12	Maximum Aperture (mm):
10	Number of Leaves:
Optical Properties	
0.8	Minimum Aperture (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- 0.8 – 12mm Adjustable Aperture
- Smooth Operation from Maximum to Minimum Aperture
- Fits in Any 25mm Cage System Plate

The TECHSPEC® Cage System Iris is a 10-leaf, blue spring steel iris in an anodized aluminum housing that can be easily integrated into any 25mm TECHSPEC Cage System plate. The TECHSPEC Cage System Iris provides smooth transition from the maximum aperture of 12mm to the minimum aperture of 0.8mm. The iris can be used to adjust system performance by controlling system f#, field stop diameter, and overall energy throughput.

Technical Information

