

TECHSPEC® 25mm Dia 0.23 NA, λ /40 Uncoated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#17-329** 3-4 DAYS

- 1 +

£616.25

ADD TO CART

Qty 1-5

£616.25

Qty 6+

£493.00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0/-0.025

Effective Focal Length EFL (mm):

50.00 @ 355nm
Numerical Aperture NA: 0.23
Back Focal Length BFL (mm): 45.10
Substrate: Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 355
Asphere Figure Error, RMS @ 632.8nm: λ/40
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 3.82
Center Thickness CT (mm): 7.20 ±0.1
f/#: 2
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Power (diopters): 20.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View