

25mm Dia. Left-Handed Plastic Circular Polarizer (CP42HE)



Stock #88-097

3-4 DAYS

-

1

+

£28.05

ADD TO CART

Qty 1-5
£28.05
Qty 6+
£23.80
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Substrate:

[CP42HE on PMMA](#)

Operating Temperature (°C):
-40 to +80

Thickness (mm):

2.29 ±0.24
Transmission (%) : 42.00
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film on PMMA
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
#Sorting : 3.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant