

TECHSPEC®

25mm Dia., UV Enhanced Aluminum,  $\lambda/10$  Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock **#14-580** 3-4 DAYS

- 1 +

£112.20

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| £112.20                       |
| Qty 6+                        |
| £89.25                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 +0.00/-0.10

Surface Flatness (P-V):

N/10

**Substrate:** [Fused Silica](#) (Coming 7980)

**Back Surface:**  
Commercial Polish

**Surface Quality:**  
20-10

**Coating Specification:**  
R<sub>avg</sub> >89% @ 250 - 450nm  
R<sub>avg</sub> >85% @ 250 - 700nm

**Coating:**  
Enhanced Aluminum (250-700nm)

**Coating Type:**  
Metal

**Clear Aperture (%):**  
90.00

**Edges:**  
Ground, protective bevel as needed

**Thickness (mm):**  
13.00 ±0.20

**Type:**  
Stemmed Mirror

**Wavelength Range (nm):**  
250 - 700

**Compatible Kinematic Mount:**  
[#58-853](#)

**Stem Diameter (mm):**  
12.50 +0.00/-0.10

**Stem Length (mm):**  
6.50 ±0.20

Regulatory Compliance

**RoHS:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)