

TECHSPEC® 25mm Dia. x 25mm FL, 8-12µm Coated Germanium Meniscus Lens



Stock **#87-967** 3-4 DAYS

- 1 + **£441.15**

ADD TO CART

Qty 1-5
£441.15
Qty 6+
£352.92
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00

Substrate: ☐
Germanium (Ge)

f/#:

1.00
Numerical Aperture NA: 0.50
Coating: BBAR (8000-12000nm)
Type: Meniscus Lens
Wavelength Range (nm): 8000 - 12000
Back Focal Length BFL (mm): 23.34
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Coating Specification: R _{avg} <3.0% @ 8 - 12µm
Edge Thickness ET (mm): 1.3
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 28.32
Radius R₂ (mm): 42.46
Surface Quality: 60-40
Wavelength Range (µm): 8 - 12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant