

TECHSPEC® 25mm Dia. x 30mm FL, Uncoated Germanium Meniscus Lens



Stock **#87-956** 3-4 DAYS

- 1 + **£340.00**

ADD TO CART

Qty 1-5
£340.00

Qty 6+
£272.00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
30.00

Substrate: ☐
Germanium (Ge)

f/#:

1.2
Numerical Aperture NA: 0.42
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Back Focal Length BFL (mm): 28.31
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Edge Thickness ET (mm): 1.5
Focal Length Specification Wavelength (μm): 10.6
Radius R ₁ (mm): 33.38
Radius R ₂ (mm): 50.04
Surface Quality: 60-40
Wavelength Range (μm): 2 - 14

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View