

TECHSPEC[®] 25mm Dia. x 35mm FL, 8-12μm Coated Germanium Meniscus Lens



Stock #87-969 3-4 DAYS

-

1

+

£441.15

ADD TO CART

Qty 1-5

£441.15

Qty 6+

£352.92

Volume Pricing

[Request Quote](#)

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
35.00

Substrate: ☐
Germanium (Ge)

f/#:

1.4
Numerical Aperture NA: 0.36
Coating: BBAR (8000-12000nm)
Type: Meniscus Lens
Wavelength Range (nm): 8000 - 12000
Back Focal Length BFL (mm): 33.29
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Coating Specification: R _{avg} <3.0% @ 8 - 12μm
Edge Thickness ET (mm): 1.6
Focal Length Specification Wavelength (μm): 10.6
Radius R₁ (mm): 38.43
Radius R₂ (mm): 57.61
Surface Quality: 60-40
Wavelength Range (μm): 8 - 12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant