

TECHSPEC[®] 25mm Dia x 50mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #46-016 3-4 DAYS

-

1

+

£59.50

ADD TO CART

Qty 1-5
£59.50
Qty 6+
£47.60
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
50.00

Substrate:

N-BK7

f/#: 2
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 47.20
Center Thickness CT (mm): 4.24
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.03
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 25.93
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
