

TECHSPEC® 25mm Dia x -100mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-669** ☐ In Stock

-

1

+

£43.77

ADD TO CART

Qty 1-5
£43.77
Qty 6+
£34.85
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-100.00

Center Thickness CT (mm):
3.00

Clear Aperture (%) : 90.00
Coating : Enhanced Aluminum (450-650nm)
Coating Specification : R _{avg} >95% @ 450 - 650nm
Coating Type : Metal
Dimensional Tolerance (mm) : +0.0/-0.1
Edge Thickness ET (mm) : 2.61
Focal Length Tolerance (%) : ±2
Radius R (mm) : 200.0
Substrate : ☐ N-BK7
Surface Accuracy : λ/2
Surface Quality : 60-40
Thickness Tolerance (mm) : ±0.1
Type : Spherical Mirror
Wavelength Range (nm) : 450 - 650

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant