

TECHSPEC® 25mm Diameter x 150mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-175 CLEARANCE 3-4 DAYS

- 1 + **£93.46**

ADD TO CART

Qty 1+

£93.46

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
150.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f#:
6.00

Numerical Aperture NA: 0.08
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 200 - 2200
Back Focal Length BFL (mm): 147.94
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 1.85
Focal Length Tolerance (%): ±3
Radius R (mm): 68.77
Surface Quality: 40-20
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View