

TECHSPEC® 25mm Diameter x 50mm FL Uncoated, UV PCX Cylinder Lens



Stock **#68-172** CLEARANCE 3-4 DAYS

- 1 + **£93.46**

ADD TO CART

Qty 1+
£93.46

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
50.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f#:
2.00

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 200 - 2200
Back Focal Length BFL (mm): 46.58
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 1.29
Focal Length Tolerance (%): ±3
Radius R (mm): 22.93
Surface Quality: 40-20
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View