

TECHSPEC® 25mm f/1.85, UCi Series Fixed Focal Length Lens



Stock #33-890 **20+ In Stock**

- 1 +

£188^{.00}

ADD TO CART

25mm UCi Series Fixed Focal Length Lens



Volume Pricing	
Qty 1+	£188.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Spec Sheets:pdf
Zemax	eDrawing:eprt
EO Spec Sheet	

General

Product Family:	UCi Series	Type:	Fixed Focal Length Lens
IR Cut Filter:	No	Imaging Lens Type:	High Performance Lens with Compact Form Factor and Fixed Aperture

Physical & Mechanical Properties

Iris Option:	Fixed	Length (mm):	31.50
Maximum Diameter (mm):	26.5	Outer Diameter (mm):	26.5
Weight (g):	38	Maximum Rear Protrusion (mm):	2.54

Optical Properties

Horizontal Field of View @ Max Sensor Format:	60.8mm - 16.4°	Field of View at Max Sensor Format:	Horizontal: 59.6mm - 16.4° Vertical: 44.6mm - 12.3° Diagonal: 74.8mm - 20.4°
Horizontal Field of View, 1/1.8" Sensor:	60.8mm - 16.4°	Horizontal Field of View, 1/2" Sensor:	54.0mm - 14.6°
Horizontal Field of View, 1/2.5" Sensor:	48.9mm - 13.2°	Horizontal Field of View, 1/3" Sensor:	40.4mm - 11.0°
Horizontal Field of View, 1/4" Sensor:	30.3mm - 8.2°	Maximum Image Circle (mm):	9.00
Numerical Aperture NA:	0.0312	Number of Elements:	7 (5)

Object Side:		(Groups):	
Focal Length FL (mm):	25.00	Working Distance (mm):	200 - ∞
Aperture (f/#):	f/1.85	Coating:	λ/4 MgF ₂
Coating Specification:	λ/4 MgF ₂	Entrance Pupil Position (mm):	15.05
Object Space Principal Plane (mm):	29.11	Image Space Principal Plane (mm):	-12.34
Maximum Distortion (%):	-0.15	Exit Pupil Position (mm):	-44.48
Lens Wavelength Range:	VIS		

Sensor

Optimized Sensor Format:	1/2.5"	Maximum Sensor Format:	1/1.8"
Pixel Size (μm):	1.85		

Threading & Mounting

Filter Thread:	N/A	Mount:	C-Mount
-----------------------	-----	---------------	---------

Environmental & Durability Factors

Storage Temperature (°C):	-20 to +60	Type of Ruggedization:	Industrial (Fixed Aperture with Simplified Mechanics)
----------------------------------	-------------------	-------------------------------	---

Regulatory Compliance

Certificate of Conformance:	View		
------------------------------------	----------------------	--	--

Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85μm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels ≤2.2μm and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

Note: For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.

UCr Series: All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC **Ingress Protection** Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.

Technical Information

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	C-Mount to M12 Adapter for UCi Lens		#12-879	£38.40 Request Quote	20+ In Stock <input type="text" value="1"/>

Related Products



#33-305 - 25mm UC Series Fixed Focal Length Lens
£208.00



#58-207 - 25mm FL f/2.5, Blue Series M12 Lens
£63.00



#59-871 - 25mm C Series Fixed Focal Length Lens
£208.00



USAF 1951 Glass Slide Resolution Targets

Frequently Purchased Together



#33-305 - 25mm UC Series Fixed Focal Length Lens
£208.00



#33-564 - 25mm Cx Series Fixed Focal Length Lens
£193.00



























#33-988 - Basler ace acA1920-40gm Monochrome GigE Camera
£464.00


























































































#34-212 - Type-A to Micro-B, USB 3.0 Locking Cable, 8m
£74.00














































Compatible Cameras











































	Title	Type	Compare	Stock Number	Price	Buy
MORE+	Allied Vision Alvim 1800 U-501m NIR, 1/2.5" 5MP C-Mount, Right Angle USB 3.1 NIR Camera (Partial Housing)	NIR Camera		#19-554	£216.00 Request Quote	CONTACT US <input type="text" value="1"/>
MORE+	Allied Vision Alvim 1800 U-501m NIR, 1/2.5" 5.0MP C-Mount, USB 3.0	NIR Camera		#19-553	£216.00 Request Quote	CONTACT US <input type="text" value="1"/>

































	Title	Type	Compare	Stock Number	Price	Buy
	NIR Camera (Partial Housing)					
MORE+ 	Allied Vision Alvium 1800 U-501m NIR, 1/2.5" 5.0MP C-Mount, USB 3.0 NIR Camera	NIR Camera		#19-547	£224.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-501m NIR, 1/2.5" 5MP C-Mount, Right Angle USB 3.1 NIR Camera	NIR Camera		#19-548	£224.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500m, 1/2.5" 5.0MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-138	£232.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500m, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-144	£232.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500c, 1/2.5" 5.0MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#14-139	£240.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500c, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#14-145	£240.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500m, 1/2.5" 5.0MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-126	£240.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500m, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-130	£240.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500c, 1/2.5" 5.0MP C-Mount, USB 3.0 Color Camera	Color Camera		#14-127	£248.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-500c, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#14-131	£248.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX064S-CC, Sony IMX178, 6.3MP, Color Camera	Color Camera		#13-702	£268.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX064S-CC-IX, Sony IMX178,	Color Camera		#13-704	£268.00 Request Quote	CONTACT US <input type="text" value="1"/> 





























	Title	Type	Compare	Stock Number	Price	Buy
	6.3MP, Color Camera					
 	LUCID Vision Labs Phoenix™ PHX064S-MC, Sony IMX178, 6.3MP, Monochrome Camera	Monochrome Camera		#13-701	£268.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX064S-MC-IX, Sony IMX178, 6.3MP, Monochrome Camera	Monochrome Camera		#13-703	£268.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX023S-CC, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-662	£296.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX023S-CC-IX, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-668	£296.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX023S-MC, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-661	£296.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX023S-MC-IX, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-667	£296.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX032S-CC, Sony IMX265, 3.2 MP, Color Camera (Recertified 05-P)	Color Camera		#11-465-RCD-05P RECERTIFIED	£300.16 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A3840-45umBAS Monochrome USB3 Basic Camera	Monochrome Camera		#16-621	£303.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace2 a2A3840-13gmBAS Monochrome GigE Basic Camera	Monochrome Camera		#16-597	£303.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-240m, 1/2.3" 2.35MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#17-085	£304.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-240c, 1/2.3" 2.35MP C-Mount, USB 3.0 Color Camera	Color Camera		#17-086	£312.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI064S-CC, Sony IMX178, 6.3MP, Color Camera	Color Camera		#13-718	£321.60 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI064S-MC, Sony IMX178, 6.3MP, Monochrome Camera	Monochrome Camera		#13-717	£321.60 Request Quote	1 In Stock <input type="text" value="1"/> 

































	Title	Type	Compare	Stock Number	Price	Buy
	Monochrome Camera					
 	Basler ace2 a2A3840-45ucBAS Color USB3 Basic Camera	Color Camera		#16-622	£322.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace2 a2A3840-13gcBAS Color GigE Basic Camera	Color Camera		#16-598	£322.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace2 a2A1920- 160umBAS Monochrome USB3 Basic Camera	Monochrome Camera		#16-617	£322.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A1920-51gmBAS Monochrome GigE Basic Camera	Monochrome Camera		#16-593	£322.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	BFS-U3-63S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#11-510	£331.20 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-PGE-63S4C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#12-756	£331.20 Request Quote	3 In Stock <input type="text" value="1"/> 
 	BFS-U3-63S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#11-509	£331.20 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-PGE-63S4M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#12-755	£331.20 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler Ace acA3088-57um USB 3.0 Monochrome Camera	Monochrome Camera		#37-213	£335.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Basler ace acA3088-16gm Monochrome GigE Camera	Monochrome Camera		#37-205	£335.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-23S3C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-748	£336.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-23S3C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#12-754	£336.80 Request Quote	4 In Stock <input type="text" value="1"/> 
 	BFS-U3-23S3M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-747	£336.80 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-23S3M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#12-753	£336.80 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI023S- CC, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-714	£337.60 Request Quote	4 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI023S- MC, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-713	£337.60 Request Quote	CONTACT US <input type="text" value="1"/> 














































	Title	Type	Compare	Stock Number	Price	Buy
	 Basler ace2 a2A1920-51gcBAS Color GigE Basic Camera	Color Camera		#16-594	£339.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium G1-240m, 1/2.3" 2.4MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-543	£344.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A1920-160ucBAS Color USB3 Basic Camera	Color Camera		#16-618	£348.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler Ace acA3088-57uc USB 3.0 Color Camera	Color Camera		#37-214	£351.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA3088-16gc Color GigE Camera	Color Camera		#37-206	£351.00 Request Quote	3 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium G1-240c, 1/2.3" 2.4MP C-Mount, GigE PoE Color Camera	Color Camera		#23-544	£352.00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium G1-500m, 1/2.5" 5MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-551	£368.00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-CC, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#11-465	£375.20 Request Quote	3 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-CC-IX, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#13-678	£375.20 Request Quote	CONTACT US <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-MC, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#11-464	£375.20 Request Quote	2 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-MC-IX, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#13-677	£375.20 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium G1-500c, 1/2.5" 5MP C-Mount, GigE PoE Color Camera	Color Camera		#23-552	£384.00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 Basler ace2 a2A3840-45umPRO Monochrome USB3 Pro Camera	Monochrome Camera		#16-633	£404.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A3840-13gmPRO Monochrome GigE Pro Camera	Monochrome Camera		#16-609	£404.00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 LUCID Vision Labs Triton™ TRI032S- CC, Sony IMX265, 3.2MP, Color Camera	Color Camera		#13-716	£416.00 Request Quote	4 In Stock <input type="text" value="1"/> 











































	Title	Type	Compare	Stock Number	Price	Buy
 	LUCID Vision Labs Triton™ TRI032S-MC, Sony IMX265, 3.2MP, Monochrome Camera	Monochrome Camera		#13-715	£416.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-875	£416.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace2 a2A3840-45ucPRO Color USB3 Pro Camera	Color Camera		#16-634	£420.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace2 a2A3840-13gcPRO Color GigE Pro Camera	Color Camera		#16-610	£420.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#14-876	£424.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	IDS U3-3880CP-C-HQ, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-544	£424.00 Request Quote	14 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-871	£424.00 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-873	£424.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	IDS U3-3880CP-M-GL, USB 3.0, 1/1.8" Monochrome Camera	Monochrome Camera		#16-545	£424.00 Request Quote	5 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A1920-160umPRO Monochrome USB3 Pro Camera	Monochrome Camera		#16-629	£428.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A1920-51gmPRO Monochrome GigE Pro Camera	Monochrome Camera		#16-605	£428.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2500-14um Monochrome USB 3.0 Camera (Recertified 05-P)	Monochrome Camera		#88-325-RCD-05P RECERTIFIED	£428.80 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, USB 3.0 Color Camera	Color Camera		#14-872	£432.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, Right Angle	Color Camera		#14-874	£432.00 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
	USB 3.1 Color Camera					
MORE+ 	Basler ace acA2500-14gm Monochrome GigE Camera	Monochrome Camera		#85-165	£432.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Triton™ TRI051S-CC, Sony IMX547, 5MP, Color Camera	Color Camera		#18-483	£436.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Triton™ TRI051S-MC, Sony IMX547, 5MP, Monochrome Camera	Monochrome Camera		#18-484	£436.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace2 a2A1920-51gcPRO Color GigE Pro Camera	Color Camera		#16-606	£448.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	BFS-PGE-31S4C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#11-528	£452.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-U3-31S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-750	£452.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	BFS-PGE-31S4M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#11-527	£452.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-U3-31S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-749	£452.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA2500-14gc Color GigE Camera	Color Camera		#85-166	£456.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace2 a2A1920-160ucPRO Color USB3 Pro Camera	Color Camera		#16-630	£456.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Basler ace acA2040-35gm Monochrome GigE Camera	Monochrome Camera		#35-915	£456.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium G1-319m, 1/1.8" 3.2MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-547	£464.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	BFLY-PGE-31S4M/C-C 1/1.8" Blackfly® PoE GigE Color Camera	Color Camera		#34-510	£468.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	BFLY-PGE-31S4M/C-C 1/1.8" Blackfly® PoE GigE Monochrome Camera	Monochrome Camera		#34-511	£468.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium G1-319c, 1/1.8" 3.2MP C-Mount, GigE PoE Color Camera	Color Camera		#23-548	£472.00 Request Quote	5 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA2040-35gc Color GigE Camera	Color Camera		#35-916	£480.00 Request Quote	2 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	M2020, 1/1.8" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#34-960	£484.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	C2020-IR, 1/1.8" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-961	£496.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA3800-10gc Color GigE Camera	Color Camera		#89-979	£496.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Mako G-319 1/1.8" Color CMOS Camera (Recertified 05-P)	Color Camera		#36-175-RCD-05P RECERTIFIED	£508.80 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	BFS-PGE-50S4C-C, PoE GigE Blackfly® S, Color Camera (Recertified 05-P)	Color Camera		#22-080-RCD-05P RECERTIFIED	£520.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	IDS U3-3270CP-C-HQ REV.2.2, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-528	£536.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA2500-14um Monochrome USB 3.0 Camera	Monochrome Camera		#88-325	£536.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-566	£536.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-565	£536.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#19-578	£544.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#19-577	£544.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#19-560	£544.00 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#19-559	£544.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, Right Angle	Color Camera		#19-572	£552.00 Request Quote	1 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
	USB 3.1 Color Camera					
MORE+ 	Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, USB 3.0 Color Camera	Color Camera		#19-571	£552.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Basler ace acA2040-55um Monochrome USB 3.0 Camera	Monochrome Camera		#35-921	£560.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Basler ace acA2500-14uc Color USB 3.0 Camera	Color Camera		#88-326	£564.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA3800-14uc Color USB 3.0 Camera	Color Camera		#89-992	£576.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA2040-55uc Color USB 3.0 Camera	Color Camera		#35-922	£576.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-PGE-50S4C-C, PoE GigE Blackfly® S, Color Camera	Color Camera		#22-080	£592.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-U3-50S4C-C, USB 3.1 Blackfly® S, Color Camera	Color Camera		#22-765	£592.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-PGE-50S4M-C, PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#22-081	£592.00 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-U3-50S4M-C, USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#22-766	£592.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium G5-500m, 1/2.5" 5MP C-Mount, 5GigE PoE Monochrome Camera	Monochrome Camera		#23-619	£600.00 Request Quote	7 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium G5-500c, 1/2.5" 5MP C-Mount, 5GigE PoE Color Camera	Color Camera		#23-620	£608.00 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	IDS U3-3890SE-C-HQ, USB 3.0, 1/1.7" Color Camera	Color Camera		#24-138	£612.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	IDS U3-3890SE-M-GL, USB 3.0, 1/1.7" Monochrome Camera	Monochrome Camera		#24-139	£612.00 Request Quote	5 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Mako G-319 1/1.8" Monochrome CMOS Camera	Monochrome Camera		#36-174	£672.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Mako G-319 1/1.8" Color CMOS Camera	Color Camera		#36-175	£688.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Manta G-0319 1/1.8" Color Camera	Color Camera		#34-717 CLEARANCE	£695.16 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	BFS-U3-32S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#36-454	£724.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-32S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#36-453	£724.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Pixelink PL- D7715CU-BL, 1/2.3" 15MP, Board Level USB 3.0 Color Camera	Color Camera		#89-400 CLEARANCE	£743.16 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2040-120um Monochrome USB 3.0 Camera	Monochrome Camera		#35-923	£784.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	PL-D775-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera	Monochrome Camera		#34-787	£796.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-120uc Color USB 3.0 Camera	Color Camera		#35-924	£800.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-0319 1/1.8" Monochrome Camera	Monochrome Camera		#34-716	£808.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	IDS U3-3070CP-C- HQ, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-512	£816.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	IDS U3-3070CP-M- GL, USB 3.0, 1/1.8" Monochrome Camera	Monochrome Camera		#16-513	£816.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-319C Color CMOS PoE Camera	Color Camera		#37-511	£856.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-319B Monochrome CMOS PoE Camera	Monochrome Camera		#37-510	£856.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	PL-D775-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera (Recertified 05-P)	Monochrome Camera		#34-787-RCD-05P RECERTIFIED	£901.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	GS3-U3-32S4C-C 1/1.8" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#33-535	£924.00 Request Quote	3 In Stock <input type="text" value="1"/> 
 	GS3-U3-32S4M-C 1/1.8" FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#33-534	£924.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL- D775CU-T, 1/2.5" 5.0MP, C-Mount USB 3.0 Color Camera	Color Camera		#89-387	£948.00 Request Quote	3 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	Pixelink PL-D7718CU-BL, 1/2.3", 18MP, C-Mount USB 3.0 Color Board Level Camera	Color Camera		#21-071	£948.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D775MU-T, 1/2.5" 5.0MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#89-386	£948.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-319C Color CMOS PoE Camera (Recertified 05-P)	Color Camera		#37-511-RCD-05P RECERTIFIED	£986.00 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D7718CU-T, 1/2.3", 18MP, C-Mount USB 3.0 Color Camera	Color Camera		#21-070	£1,036.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink M-Series M18C-CYL Microscopy Color Camera	Color Microscopy Camera		#21-072	£1,208.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	M2050, 1/1.8" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera	Monochrome Camera		#16-024	£1,280.00 Request Quote	4 In Stock <input type="text" value="1"/> 
 	C2050-IR, 1/1.8" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera	Color Camera		#16-025	£1,292.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Oryx® ORX-10GS-32S4C-C Color 10GigE	Color Camera		#19-797	£1,420.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Oryx® ORX-10GS-32S4M-C Mono 10GigE	Monochrome Camera		#19-796	£1,420.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas10 ATX051S-CC, Sony IMX537, 5.0MP, Color Camera	Color Camera		#18-477	£1,524.00 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas10 ATX051S-MC, Sony IMX537, 5.0MP, Monochrome Camera	Monochrome Camera		#18-478	£1,524.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	PL-D7718CU-AFE Pixelink USB 3.0 Autofocus Color Camera	Color Camera		#21-078	£1,668.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Lumenera INFINITY5 5-3 Microscopy Color Camera	Color Microscopy Camera		#16-678	£2,980.00 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Lumenera INFINITY5 5-3 Microscopy Monochrome Camera	Monochrome Microscopy Camera		#16-677	£2,980.00 Request Quote	1 In Stock <input type="text" value="1"/> 

Resources

Media Type

- Application Note
- Video
- Published Article
- FAQ
- Glossary
- Technical Tool

APPLICATION NOTE
Anti-Reflection (AR) Coatings

APPLICATION NOTE
An Introduction to Optical Coatings

VIDEO
Wavelength and f#

APPLICATION NOTE
Understanding Focal Length and Field of View

APPLICATION NOTE
Introduction to Modulation Transfer Function

WEBINARS
Choosing the Right Machine Vision Lens

[View More](#)