

25mm Fixed Focal Length Lens



#86-210



Stock #86-208 3-4 DAYS



1



£1,394.00

ADD TO CART

Qty 1+

£1,394.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
125.00

Iris Option:
Variable

Length (mm):
89.00

Filter Thread:

M40.5 x 0.50
Maximum Diameter (mm): 45.0
Weight (g): 250.00
Maximum Image Circle (mm): 21.60
Horizontal Field of View @ Max Sensor Format: 40.9
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Maximum Sensor Format: 4/3"
Working Distance (mm): 150 - ∞
Mount: C-Mount
Aperture (f/#): f/2 - f/16
Distortion (%): <-0.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)