

25mm FL, T-Mount Focusing Assembly



Stock **#53-044** 1 In Stock

-

1

+

£97⁶⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£97.60 each
Qty 10-24	£87.84 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Accessory

Type of Illumination:

Physical & Mechanical Properties	
55.00	Total Length (mm):
48.00	Outer Diameter (mm):
Optical Properties	
15.4	Beam Divergence (°):
25.00	Focal Length FL (mm):
1.6	Spot Size at 6" Working Distance (inches):
Threading & Mounting	
T-mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Reduce Divergence of Fiber Optic Light Guides
- Available in C- or T-Mount or Slim Mount
- Shape Output over Small Areas

Fiber-Lite Focusing Lenses are an essential component in reducing divergence of fiber optic light guides. Fiber optic light guides project a large, diffuse beam of light – not a collimated or focused spot. Lens assemblies at the end of the fiber can collect light efficiently and shape the output effectively over smaller areas. Fiber-Lite Focusing Lenses are available in two configurations – mounted in our C- and T-Mbunt components, or in a slim mount for direct integration with many of our light guides. The C- and T-Mbunt configuration requires a standard [Dolan-Jenner adapter](#), and can be used with any light guide. Additional accessories may be added with our [C- and T-Mount components](#). Stock [#58-837](#) can be used with any of our 1/8" or 1/4" light guides with tip diameters of 0.187" or 0.312". [#58-836](#) can be used with our semi-rigid and hybrid light guides with end-tip diameter of 0.500".