

TECHSPEC® 25mm H x 50mm L x -150mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#68-068** 3-4 DAYS

⊖ 1 ⊕ **£91.80**

ADD TO CART

Qty 1-5

£91.80

Qty 6+

£73.10

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-150.00

Substrate: ☐
[N-BK7](#)

Coating:
Uncoated

Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -152.64
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 4.97
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -77.52
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View