

**TECHSPEC® 25mm ID Side Access Mounting Plate, 60° Cutout**



#85-640

Stock **#85-640** [CONTACT US](#)

- 1 + £47<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£47.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Fixed **Function:**

Black Anodized Aluminum **Note:**

**Physical & Mechanical Properties**

25.0 **Plate Inner Diameter (mm):**

**Bolt Circle Diameter for 6mm Dia. Thru (mm):**

38.0

**Bolt Circle Diameter for M3 C'bore (mm):**

38.0

**Dimensions (mm):**

50 Dia.

**Thickness (mm):**

10.00

## Threading & Mounting

**Mounting Threads:**

C'Bore Holes: (8) M3  
Rod Thru Holes: (4) 6  
60° cutout for side access

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 233:**

[Compliant](#)

## Product Details

- Specialized Plates Designed to Hold and Position Optics
- Filter Holder Plate with Interchangeable Filter Holder

These specialized TECHSPEC® Cage System Filter Holder Plates and Filter Holders are designed to hold and position a range of [optical components](#). Like a standard cage system plate, the anodized aluminum, U-shaped Filter Holder Plate features 6mm rod holes, in addition to being able to accept a Delrin® interchangeable filter holder that easily slides into the filter holder plate.

### Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Filter Holder Plate and Interchangeable Filter Holder](#).