

TECHSPEC[®] 25mm ID Standard Cage Plate with M6 for Post Mounting



25mm ID Standard Cage Plate with M6 for Post Mounting, #85-632

Stock **#85-632** 20+ In Stock

-

1

+

£35⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£35.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Function:

Fixed

Physical & Mechanical Properties

Plate Inner Diameter (mm):

25.0

Bolt Circle Diameter for 6mm Dia. Thru (mm):

38.0

Bolt Circle Diameter for M3 C'bore (mm):

38.0	
Black Anodized Aluminum	Construction:
Diameter Tolerance (mm): +0.025/-0.000 (inner diameter)	
50 Dia.	Dimensions (mm):
10.00	Thickness (mm):

Threading & Mounting

	Compatible Post:
M6 x 1.0	

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Fundamental for Basic Cage System Structure
- 50mm Diameter or 2" Square
- Anodized Aluminum Construction

TECHSPEC® Cage System Mounting Plates are fundamental components of TECHSPEC® Cage Systems. Each plate has four 6mm rod holes for constructing a basic cage system structure. Rods are mounted within 38mm bolt circles for a 26.9mm separation, and are secured in place using the included M3 x2.5 set screws. TECHSPEC® Cage System Mounting Plates includes three M3 x6 set screws for securing optical components, [cage system tubes](#), or mounts within the plate's inner diameter. These plates are constructed of black anodized aluminum and have dimensions and diameters.

Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Interchangeable Optical Mount and Side Access Mounting Plate](#) and [Four-Rod Insertion Plate](#)