

TECHSPEC® 25mm Schmidt-Pechan Prism



TECHSPEC® Pechan Prism

Stock #36-039 3-4 DAYS

- 1 + **£420.75**

ADD TO CART

Qty 1-5

£420.75

Qty 6+

£336.60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
VIS 0° & Aluminized

Substrate: ☐
[N-BK7](#)

Height (mm):
50.45

Surface Quality: 40-20
Thickness (mm): 32.04
Type: Schmidt-Pechan Prism
Dimensional Tolerance (mm): ±0.1
Image Orientation: Right-Handed
Coating Specification: Entrance/Exit Faces: R_{avg} ≤0.4% @ 425 - 675nm Roof: R_{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 0
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/8
Width (mm): 29.00
Ray Deviation Tolerance (arcmin): ±10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View