

25mm Standard UV Fixed Focal Length Lens



25mm Standard UV Fixed Focal Length Lens, #57-542

Stock **#57-542** 3-4 DAYS

- 1 + **£1,530.00**

ADD TO CART

Qty 1+
£1,530.00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
58.9

Iris Option:
Variable

Length (mm):
25.40

Horizontal Field of View, 1/2" Sensor:
58.9mm - 14.0°

Filter Thread:

M25.5 x0.50
Maximum Diameter (mm): 30.0
Weight (g): 33.00
Maximum Image Circle (mm): 16.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Maximum Sensor Format: 1"
Working Distance (mm): 230 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8 - f/16
Lens Wavelength Range: UV-NIR

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View